

Reverse Polarity SMA Male to Reverse Polarity SMA Male Adapter



TECHNICAL DATA SHEET

Reverse Polarity SMA Male to Reverse Polarity SMA Male Adapter

Configuration

Connector 1 Impedance 1 Connector Specification 1 Connector 2 Impedance 2 Connector Specification 2 Adapter Design Body Style

Mechanical Specifications

Size

Length, in [mm] Width/Dia., in [mm]

Connector 1

Type Inner Conductor Material and Plating Inner Conductor Plating Specification Coupling Nut Material and Plating Coupling Nut Plating Specification Hex Size, Inch Torque, in-Ibs [Nm] Body Material and Plating Body Plating Specification Dielectric Type

Connector 2

Type Inner Conductor Material and Plating Inner Conductor Plating Specification Coupling Nut Material and Plating Coupling Nut Plating Specification Hex Size, Inch Torque, in-Ibs [Nm] Body Material and Plating Body Plating Specification Dielectric Type SMA Male Reverse Polarity 50 Ohms MIL-STD-348 SMA Male Reverse Polarity 50 Ohms MIL-STD-348 Standard Straight

0.86 [21.84] 0.312 [7.92]

SMA Male Reverse Polarity Beryllium Copper, Gold MIL-G-45204, Type II, Class 2 Passivated Stainless Steel QQ-P-35 5/16 8 [0.9] Passivated Stainless Steel QQ-P-35 Teflon

SMA Male Reverse Polarity Beryllium Copper, Gold MIL-G-45204, Type II, Class 2 Passivated Stainless Steel QQ-P-35 5/16 8 [0.9] Passivated Stainless Steel QQ-P-35 Teflon

Compliance Certifications (visit www.Pasternack.com for current document) RoHS Compliant Yes

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Reverse Polarity SMA Male to Reverse Polarity SMA Male Adapter PE9590

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com



PE9590



Reverse Polarity SMA Male to Reverse Polarity SMA Male Adapter



PE9590

TECHNICAL DATA SHEET

Plotted and Other Data Notes:

Values at 25 °C, sea level

URL: http://www.pasternack.com/sma-male-sma-male-straight-adapter-pe9590-p.aspx

Reverse Polarity SMA Male to Reverse Polarity SMA Male Adapter from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com



2

PE9590 CAD Drawing Reverse Polarity SMA Male to Reverse Polarity SMA Male Adapter

